




Inductive sensor

IA-2010-ABOA/VDE/O.LED/6M

Article no longer available - archive entry

Alternative articles: IA0017

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Output function		normally open
Sensing range	[mm]	10
Housing		tubular
Dimensions	[mm]	Ø 20

Electrical data

Operating voltage	[V]	20...250 AC/DC
Protection class		II
Reverse polarity protection		yes

Outputs

Output function		normally open
Max. voltage drop switching output DC	[V]	6
Max. voltage drop switching output AC	[V]	6.5
Minimum load current	[mA]	5
Max. leakage current	[mA]	2.5 (250 V AC) / 1.3 (110 V AC) / 0.8 (24 V DC)
Permanent current rating of switching output AC	[mA]	250; (350 (...50 °C))
Permanent current rating of switching output DC	[mA]	100



Inductive sensor

IA-2010-ABOA/VDE/O.LED/6M

Short-time current rating of switching output	[mA]	2200; (20 ms / 0,5 Hz)
Switching frequency AC	[Hz]	25
Switching frequency DC	[Hz]	70
Short-circuit protection		no
Overload protection		no
Monitoring range		
Sensing range	[mm]	10
Real sensing range Sr	[mm]	10 ± 10 %
Operating distance	[mm]	0...8.1
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2
Hysteresis	[% of Sr]	1...15
Switch-point drift	[% of Sr]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
Mechanical data		
Housing		tubular
Mounting		non-flush mountable
Dimensions	[mm]	Ø 20
Material		PBT
Accessories		
Items supplied	Mounting clamp: 1	
Remarks		
Pack quantity	1 pcs.	

IA0046




Inductive sensor

IA-2010-ABOA/VDE/O.LED/6M

Electrical connection

Cable: 6 m, rubber; 2 x 0.75 mm²

Connection



BN = Core colors :
brown
BU = blue