


# EVC960



## Female cordset

ADOAH050MSE0005C05



Application		
System	Halogen-free; gold-plated contacts; screened cable; Drag chain suitability	
Application	CAN bus	
Electrical data		
Operating voltage	[V]	32 DC; (wires 4+5: 5 V)
Max. current load total	[A]	4; (wires 4+5: 0,05 A)
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection	IP 67; IP 68; IP 69K	
Mechanical data		
Weight	[g]	490.05
Dimensions	[mm]	38 x 15.5 x 31.5
Molded-body material	TPU (urethane)	
Material nut	brass, nickel-plated	
Sealing material	FKM	
Drag chain suitability	yes	
Drag chain suitability	Bending radius for flexible applications	min. 10 x cable diameter
	Travel speed	max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s²
	Bending cycles	> 5 Mio.
	Torsional strain	± 180 °/m
Remarks		
Remarks	The CAN bus terminating resistor (120 Ω) is integrated in the M12 connector.	
Pack quantity	1 pcs.	

# EVC960



## Female cordset


ADOAH050MSE0005C05

### Electrical connection


Cable: 5 m, PUR, Halogen-free, lilac, Ø 8.4 mm, screened; red / black: 2 x 0.75 mm<sup>2</sup> (42 x Ø 0.15 mm ) + white / blue: 2 x 0.5 mm<sup>2</sup> (19 x Ø 0.19 mm ) + screen: 1 x 0.75 mm<sup>2</sup> (42 x Ø 0.15 mm )

### Electrical connection - Socket

Connector: 1 x M12, angled; coding: A; Moulded body: TPU (urethane), black; Locking: brass, nickel-plated; sealing: FKM; Contacts: gold-plated; Tightening torque: 0.6...1.5 Nm



### Connection



	Core colors :
BK =	black
BU =	blue
RD =	red
WH =	white
screen =	screen