



Inductive sensor

IA-3010-APKG/20m

Article no longer available - archive entry



Product characteristics

Electrical design	PNP
Output function	normally closed
Sensing range [mm]	10
Housing	tubular
Dimensions [mm]	Ø 20 / L = 77

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	15; (24 V)
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally closed
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	300
Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)
Overload protection	yes

Monitoring range

Sensing range [mm]	10
Real sensing range Sr [mm]	10 ± 10 %
Operating distance [mm]	0...8.1

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2
Hysteresis [% of Sr]	1...15
Switch-point drift [% of Sr]	-10...10

Operating conditions

Ambient temperature [°C]	-25...80
--------------------------	----------

IA5053



Inductive sensor

IA-3010-APKG/20m

Protection	IP 67
------------	-------

Tests / approvals

EMC	EN 60947-5-2
MTTF [years]	1844

Mechanical data

Housing	tubular
Mounting	non-flush mountable
Dimensions [mm]	Ø 20 / L = 77
Material	PBT

Displays / operating elements

Display	Switching status	1 x LED, yellow
---------	------------------	-----------------

Accessories

Items supplied	Mounting clamp: 1
----------------	-------------------


Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 20 m, PVC; 3 x 0.5 mm²

Connection



BN = Core colors : brown
BU = blue
BK = black