

IA9213




Inductive sensor

IA-2010-ARKG/UP/6M

Article no longer available - archive entry

Alternative articles: IA5122
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics		
Electrical design		PNP/NPN
Output function		normally open
Sensing range	[mm]	10
Housing		tubular
Dimensions	[mm]	Ø 20
Electrical data		
Operating voltage	[V]	10...55 DC
Protection class		I
Reverse polarity protection		yes
Outputs		
Electrical design		PNP/NPN
Output function		normally open
Max. voltage drop switching output DC	[V]	4.6
Minimum load current	[mA]	4
Max. leakage current	[mA]	0.6
Permanent current rating of switching output DC	[mA]	400
Switching frequency DC	[Hz]	500
Short-circuit protection		yes

IA9213



Inductive sensor

IA-2010-ARKG/UP/6M

Type of short-circuit protection	yes (non-latching)	
Overload protection	yes	
Monitoring range		
Sensing range	[mm]	10
Real sensing range Sr	[mm]	10 ± 10 %
Operating distance	[mm]	0...8.1
Accuracy / deviations		
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2	
Hysteresis	[% of Sr]	1...15
Switch-point drift	[% of Sr]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection	IP 67	
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Housing	tubular	
Mounting	non-flush mountable	
Dimensions	[mm]	Ø 20
Material	PBT	
Displays / operating elements		
Display	Switching status	1 x LED, yellow
Accessories		
Items supplied	Mounting clamp: 1	
Remarks		
Pack quantity	1 pcs.	

IA9213



Inductive sensor

IA-2010-ARKG/UP/6M

Electrical connection

Cable: 6 m, PVC; 2 x 0.34 mm²

Connection



BK =

Core colors :
black