


Inductive sensor

IB-2020-ABOA/MS/10M

Article no longer available - archive entry

Alternative articles: IB0012

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Output function		normally open
Sensing range	[mm]	20
Housing		tubular
Dimensions	[mm]	Ø 34 / L = 82

Electrical data

Operating voltage	[V]	20...250 AC/DC
Reverse polarity protection		no

Outputs


Output function		normally open
Max. voltage drop switching output DC	[V]	6.5
Max. voltage drop switching output AC	[V]	6.5
Minimum load current	[mA]	5
Max. leakage current	[mA]	2.5 (250 V AC) / 1.3 (110 V AC) / 0.8 (24 V DC)
Permanent current rating of switching output AC	[mA]	250; (350 (...50 °C))
Permanent current rating of switching output DC	[mA]	100
Short-time current rating of switching output	[mA]	2200; (20 ms / 0,5 Hz)
Switching frequency AC	[Hz]	20
Switching frequency DC	[Hz]	70
Short-circuit protection		no
Overload protection		no



Inductive sensor

IB-2020-ABOA/MS/10M

Monitoring range		
Sensing range	[mm]	20
Real sensing range Sr	[mm]	20 ± 10 %
Operating distance	[mm]	0...16.2
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.4 / copper: 0.3
Hysteresis	[% of Sr]	3...15
Switch-point drift	[% of Sr]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Housing		tubular
Mounting		non-flush mountable
Dimensions	[mm]	Ø 34 / L = 82
Material		housing: PBT; end cap: brass nickel-plated; PG cable gland: brass nickel-plated
Displays / operating elements		
Display	Switching status	1 x LED, yellow
Accessories		
Items supplied		Mounting clamp: 1
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 10 m, silicone; 2 x 0.75 mm ²		
Connection		



BN = Core colors :
brown
BU = blue