




Inductive sensor

IBE2020-FRKG

Article no longer available - archive entry

Alternative articles: IB5124

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Output function		normally open / closed; (selectable)
Sensing range	[mm]	20
Housing		tubular
Dimensions	[mm]	Ø 34 / L = 98

Electrical data

Operating voltage	[V]	10...55 DC
Reverse polarity protection		yes

Outputs

Output function		normally open / closed; (selectable)
Max. voltage drop switching output DC	[V]	4.6
Minimum load current	[mA]	4
Max. leakage current	[mA]	1
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	40
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes

Monitoring range

Sensing range	[mm]	20
Real sensing range Sr	[mm]	20 ± 10 %
Operating distance	[mm]	0...16.2

Accuracy / deviations

Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.54 / aluminum: 0.5 / copper: 0.46
-------------------	--	--

IB5032



Inductive sensor

IBE2020-FRKG

Hysteresis	[% of Sr]	1...15
Switch-point drift	[% of Sr]	-10...10

Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 65

Tests / approvals

EMC	EN 60947-5-2
-----	--------------

Mechanical data

Housing	tubular
Mounting	non-flush mountable
Dimensions	[mm] Ø 34 / L = 98
Material	PBT; end cap: PC

Displays / operating elements

Display	Switching status	1 x LED, yellow
---------	------------------	-----------------

Accessories

Items supplied	Mounting clamp: 1
----------------	-------------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

terminals: ...2.5 mm²

Connection

