


IB5162



Inductive sensor

IBE3020-FPKG/US-100-KPX



Product characteristics

Electrical design		PNP
Output function		normally open / closed; (selectable)
Sensing range	[mm]	20
Housing		tubular
Dimensions	[mm]	Ø 34

Electrical data

Operating voltage	[V]	10...36 DC
Current consumption	[mA]	15; (24 V)
Protection class		II
Reverse polarity protection		yes

Outputs


Electrical design		PNP
Output function		normally open / closed; (selectable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	350
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes

IB5162



Inductive sensor

IBE3020-FPKG/US-100-KPX

Monitoring range		
Sensing range	[mm]	20
Real sensing range Sr	[mm]	20 ± 10 %
Operating distance	[mm]	0...16.2
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.4 / copper: 0.3
Hysteresis	[% of Sr]	3...15
Switch-point drift	[% of Sr]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 65
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
MTTF	[years]	2450
Mechanical data		
Weight	[g]	186
Housing		tubular
Mounting		non-flush mountable
Dimensions	[mm]	Ø 34
Material		PBT; end cap: PC
Displays / operating elements		
Display	Switching status	1 x LED, yellow
Accessories		
Accessories (supplied)		Mounting clamp: 1
Remarks		
Pack quantity		1 pcs.
Electrical connection - plug		
Connector: 1 x M12		
		

IB5162



Inductive sensor

IBE3020-FPKG/US-100-KPX

Connection

