


IB5169



Inductive sensor

IB-2020-FRKG/US-104-IRF



Product characteristics

Electrical design	PNP/NPN
Output function	normally open / closed; (selectable)
Sensing range [mm]	20
Housing	tubular
Dimensions [mm]	Ø 34 / L = 95

Application

System	gold-plated contacts
--------	----------------------

Electrical data

Operating voltage [V]	10...36 DC
-----------------------	------------

IB5169



Inductive sensor

IB-2020-FRKG/US-104-IRF

Protection class	II	
Reverse polarity protection	yes	
Outputs		
Electrical design	PNP/NPN	
Output function	normally open / closed; (selectable)	
Max. voltage drop switching output DC [V]	4.6	
Minimum load current [mA]	4	
Max. leakage current [mA]	1	
Permanent current rating of switching output DC [mA]	250	
Switching frequency DC [Hz]	200	
Short-circuit protection	yes	
Overload protection	yes	
Monitoring range		
Sensing range [mm]	20	
Real sensing range Sr [mm]	20 ± 10 %	
Operating distance [mm]	0...16.2	
Accuracy / deviations		
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.4 / copper: 0.3	
Hysteresis [% of Sr]	1...15	
Switch-point drift [% of Sr]	-10...10	
Operating conditions		
Ambient temperature [°C]	-25...70	
Protection	IP 67	
Tests / approvals		
EMC	EN 60947-5-2	
MTTF [years]	1941	
Mechanical data		
Weight [g]	226	
Housing	tubular	
Mounting	non-flush mountable	
Dimensions [mm]	Ø 34 / L = 95	
Material	housing: PBT; sensing face: PBT orange; clamp: PBT black	
Displays / operating elements		
Display	Switching status	4 x 90° LED, yellow
Accessories		
Items supplied	Mounting clamp: 1	
Remarks		
Pack quantity	1 pcs.	

IB5169



Inductive sensor

IB-2020-FRKG/US-104-IRF

Electrical connection - plug

Connector: 1 x M12; coding: A; Locking: brass, weld coated; Contacts: gold-plated

