




## Inductive sensor

IGK3015-APKG/K1/V4A/US-104



## Product characteristics

|                    |                  |
|--------------------|------------------|
| Electrical design  | PNP              |
| Output function    | normally closed  |
| Sensing range [mm] | 15               |
| Housing            | Threaded type    |
| Dimensions [mm]    | M18 x 1 / L = 60 |

## Application

|                                          |                                                                                                                                                            |
|------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|
| System                                   | gold-plated contacts; Increased sensing range; correction factor = 1; Magnetic-field immune                                                                |
| Application                              | material handling; refrigerated warehouse / shock freezing; Suitable for industrial, mobile, cooling and lubricating applications; Industrial applications |
| Magnetic-field immune                    | yes                                                                                                                                                        |
| Max. electromagnetic field immunity [mT] | 300                                                                                                                                                        |

## Electrical data

|                             |            |
|-----------------------------|------------|
| Operating voltage [V]       | 10...30 DC |
| Current consumption [mA]    | < 20       |
| Protection class            | III        |
| Reverse polarity protection | yes        |

## Outputs

|                                                      |                 |
|------------------------------------------------------|-----------------|
| Electrical design                                    | PNP             |
| Output function                                      | normally closed |
| Max. voltage drop switching output DC [V]            | 2.5             |
| Permanent current rating of switching output DC [mA] | 100             |
| Switching frequency DC [Hz]                          | 2000            |
| Short-circuit protection                             | yes             |
| Overload protection                                  | yes             |

## Monitoring range

|                               |                |
|-------------------------------|----------------|
| Sensing range [mm]            | 15             |
| Real sensing range $S_r$ [mm] | $15 \pm 10 \%$ |
| Operating distance [mm]       | 0...12.15      |
| Increased sensing range       | yes            |



## Inductive sensor

IGK3015-APKG/K1/V4A/US-104

| Accuracy / deviations         |                                                                                                                       |                                                                                  |
|-------------------------------|-----------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------|
| Correction factor             | steel: 1 / stainless steel: 1 / brass: 1 / aluminum: 1 / copper: 1                                                    |                                                                                  |
| Hysteresis [% of Sr]          | 3...15                                                                                                                |                                                                                  |
| Switch-point drift [% of Sr]  | -10...10                                                                                                              |                                                                                  |
| Correction factor = 1         | yes                                                                                                                   |                                                                                  |
| Operating conditions          |                                                                                                                       |                                                                                  |
| Ambient temperature [°C]      | -40...85                                                                                                              |                                                                                  |
| Protection                    | IP 65; IP 66; IP 67; IP 68; IP 69K                                                                                    |                                                                                  |
| Tests / approvals             |                                                                                                                       |                                                                                  |
| EMC                           | EN 61000-4-2 ESD                                                                                                      | 4 kV CD / 8 kV AD                                                                |
|                               | EN 61000-4-3 HF radiated                                                                                              | 10 V/m                                                                           |
|                               | EN 61000-4-4 Burst                                                                                                    | 2 kV                                                                             |
|                               | EN 61000-4-6 HF conducted                                                                                             | 10 V                                                                             |
|                               | EN 55011                                                                                                              | class B                                                                          |
| Vibration resistance          | EN 60068-2-6 Fc                                                                                                       | 20 g 11 ms half-sine; 3 shocks each in every direction of the 3 coordinate axes  |
| Shock resistance              | EN 60068-2-27 Ea                                                                                                      | 100 g 11 ms half-sine; 3 shocks each in every direction of the 3 coordinate axes |
| Continuous shock resistance   | EN 60068-2-27                                                                                                         | 40 g 6 ms; 4000 shocks each in every direction of the 3 coordinate axes          |
| Fast temperature changes      | EN 60068-2-14 Na                                                                                                      | TA = -40 °C; TB = 85 °C; t1 = 30 min; t2 = < 10 s; 50 cycles                     |
| Salt spray test               | EN 60068-2-52 Kb                                                                                                      | severity level 5 (4 test cycles)                                                 |
| MTTF [years]                  | 469                                                                                                                   |                                                                                  |
| Embedded software included    | yes                                                                                                                   |                                                                                  |
| UL approval                   | UL approval number                                                                                                    | A005                                                                             |
| Mechanical data               |                                                                                                                       |                                                                                  |
| Weight [g]                    | 40.2                                                                                                                  |                                                                                  |
| Housing                       | Threaded type                                                                                                         |                                                                                  |
| Mounting                      | non-flush mountable                                                                                                   |                                                                                  |
| Dimensions [mm]               | M18 x 1 / L = 60                                                                                                      |                                                                                  |
| Thread designation            | M18 x 1                                                                                                               |                                                                                  |
| Material                      | stainless steel (1.4404 / 316L); sensing face: LCP white; LED window: PEI; lock nuts: stainless steel (1.4404 / 316L) |                                                                                  |
| Displays / operating elements |                                                                                                                       |                                                                                  |
| Display                       | Switching status                                                                                                      | 4 x LED, yellow                                                                  |
| Accessories                   |                                                                                                                       |                                                                                  |
| Items supplied                | lock nuts: 2                                                                                                          |                                                                                  |
| Remarks                       |                                                                                                                       |                                                                                  |
| Pack quantity                 | 1 pcs.                                                                                                                |                                                                                  |

## Inductive sensor


IGK3015-APKG/K1/V4A/US-104

### Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: gold-plated



### Connection



### Diagrams and graphs

#### Installation

