

ID5029




Inductive sensor

ID-3050-BNKG

Article no longer available - archive entry

Alternative articles: ID5023

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Electrical design	NPN
Output function	normally closed
Sensing range [mm]	50
Housing	rectangular
Dimensions [mm]	120 x 80 x 30

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	15; (24 V)
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	NPN
Output function	normally closed
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	8
Short-circuit protection	yes

ID5029



Inductive sensor

ID-3050-BNKG

Type of short-circuit protection	yes (non-latching)	
Overload protection	yes	
Monitoring range		
Sensing range [mm]	50	
Sensing range adjustable	yes	
Factory setting sensing range [mm]	50	
Real sensing range Sr [mm]	50 ± 10 %	
Operating distance [mm]	0...40.5	
Accuracy / deviations		
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2	
Hysteresis [% of Sr]	1...15	
Switch-point drift [% of Sr]	-10...10	
Operating conditions		
Ambient temperature [°C]	-25...80	
Protection	IP 65	
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Housing	rectangular	
Mounting	non-flush mountable	
Dimensions [mm]	120 x 80 x 30	
Material	PPE modified	
Displays / operating elements		
Display	Switching status	1 x LED, yellow
Accessories		
Items supplied	screwdriver: 1	
Remarks		
Pack quantity	1 pcs.	

ID5029




Inductive sensor

ID-3050-BNKG

Electrical connection

Cable: 2 m, PVC; 3 x 0.5 mm²

Connection



BN =	Core colors :
BU =	brown
BK =	blue
	black