


## Inductive sensor

IEB3001-BNOG/10m

Article no longer available - archive entry



## Product characteristics

Electrical design	NPN
Output function	normally closed
Sensing range [mm]	1
Housing	Threaded type
Dimensions [mm]	M8 x 1 / L = 35

## Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	15; (24 V)
Protection class	III
Reverse polarity protection	no

## Outputs

Electrical design	NPN
Output function	normally closed
Max. voltage drop switching output DC [V]	1
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	750
Notes on switching frequency [Hz]	1000 nb
Short-circuit protection	no
Overload protection	no

## Monitoring range

Sensing range [mm]	1
Real sensing range Sr [mm]	1 ± 10 %
Operating distance [mm]	0...0.8

## Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2
Hysteresis [% of Sr]	1...15
Switch-point drift [% of Sr]	-10...10

## Operating conditions

Ambient temperature [°C]	-25...80
--------------------------	----------

# IE5088



## Inductive sensor

IEB3001-BNOG/10m

Protection	IP 67
------------	-------

### Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B
MTTF	[years]	2673

### Mechanical data

Housing	Threaded type
Mounting	flush mountable
Dimensions	[mm] M8 x 1 / L = 35
Thread designation	M8 x 1
Material	brass white bronze coated; PBT

### Displays / operating elements

Display	Switching status	1 x LED, yellow
---------	------------------	-----------------

### Accessories

Items supplied	lock nuts: 2
----------------	--------------


### Remarks

Pack quantity	1 pcs.
---------------	--------

### Electrical connection

Cable: 10 m, PVC; 3 x 0.14 mm<sup>2</sup>

### Connection



	Core colors :
BN =	brown
BU =	blue
BK =	black