


IE5155



Inductive sensor

IEA3001-BNOG/V4A 10m

Article no longer available - archive entry



Product characteristics

Electrical design		NPN
Output function		normally closed
Sensing range	[mm]	1
Housing		Threaded type
Dimensions	[mm]	M8 x 1 / L = 50

Electrical data

Operating voltage	[V]	10...36 DC
Current consumption	[mA]	15; (24 V)
Protection class		III
Reverse polarity protection		no

Outputs

Electrical design		NPN
Output function		normally closed
Max. voltage drop switching output DC	[V]	1
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	750
Notes on switching frequency		1000 nb
Short-circuit protection		no
Overload protection		no

Monitoring range

Sensing range	[mm]	1
Real sensing range S_r	[mm]	$1 \pm 10\%$
Operating distance	[mm]	0...0.8

Accuracy / deviations

Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2
Hysteresis	[% of S_r]	1...15
Switch-point drift	[% of S_r]	-10...10


IE5155



Inductive sensor

IEA3001-BNOG/V4A 10m

Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Housing		Threaded type
Mounting		flush mountable
Dimensions	[mm]	M8 x 1 / L = 50
Thread designation		M8 x 1
Material		stainless steel (1.4571/316Ti); PBT
Displays / operating elements		
Display	Switching status	1 x LED, yellow
Accessories		
Accessories (supplied)		lock nuts: 2
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 10 m, PVC; 3 x 0.14 mm ²		
Connection		



Core colors :

BN = brown
BU = blue
BK = black

Article no longer available - archive entry