

Inductive sensor

IEB3001-BPOG/6M/PH

Article no longer available - archive entry



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	1
Housing	Threaded type
Dimensions [mm]	M8 x 1 / L = 35

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	10; (24 V)
Protection class	II
Reverse polarity protection	no

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	1
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	750
Notes on switching frequency [Hz]	1000 nb
Short-circuit protection	no
Overload protection	no

Monitoring range

Sensing range [mm]	1
Real sensing range Sr [mm]	1 ± 10 %
Operating distance [mm]	0...0.8

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.4 / copper: 0.3
Hysteresis [% of Sr]	3...15
Switch-point drift [% of Sr]	-10...10

Operating conditions

Ambient temperature [°C]	-25...80
--------------------------	----------

IE5200



Inductive sensor

IEB3001-BPOG/6M/PH

Protection	IP 67
------------	-------

Tests / approvals

MTTF	[years]	2804
------	---------	------

Mechanical data

Housing	Threaded type
Mounting	flush mountable
Dimensions [mm]	M8 x 1 / L = 35
Thread designation	M8 x 1
Material	brass nickel-plated; PBT

Displays / operating elements

Display	Switching status	1 x LED, yellow
---------	------------------	-----------------

Accessories

Items supplied	lock nuts: 2
----------------	--------------


Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 6 m, PUR; highly flexible; 3 x 0.14 mm²

Connection



BK = Core colors :
BN = black
BU = brown
blue