


EVW153



Connection cable

VDOAH043SCS02,5T04STGH040SCS



Application

System	Free from silicone; Halogen-free; gold-plated contacts; Drag chain suitability
Application	welding applications
Free from silicone	yes

Electrical data

Operating voltage [V]	10...36 DC
Protection class	II
Max. current load total [A]	4

Outputs

Electrical design	PNP
-------------------	-----

Operating conditions

Ambient temperature [°C]	-25...90
Note on ambient temperature	cULus: ...75
Ambient temperature (moving) [°C]	-25...90
Note on ambient temperature (moving)	cULus: ...75
Protection	IP 65; IP 67; IP 68; IP 69K

Mechanical data

Weight [g]	122
Dimensions [mm]	15.5 x 15.5 x 49.5
Molded-body material	TPU (urethane)
Material nut	brass, weld coated
Sealing material	FKM



Connection cable

VDOAH043SCS02,5T04STGH040SCS

Drag chain suitability	yes	
Drag chain suitability	Bending radius for flexible applications	min. 10 x cable diameter
	Travel speed	max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s ²
	Bending cycles	> 2 Mio.
	Torsional strain	± 180 °/m

Displays / operating elements

Display	Switching status	2 x LED, yellow
	Power	1 x LED, green

Remarks

Remarks	with 2 label holders 30 mm long	
Pack quantity	1 pcs.	

Electrical connection - plug


Connector: 1 x M12, straight; coding: A; Moulded body: TPU (urethane), orange; Locking: brass, weld coated; Contacts: gold-plated; Tightening torque: 0.6...1.5 Nm



Electrical connection

Cable: 2.5 m, PUR, Halogen-free, orange, Ø 4.9 mm; not irradiated (can be recycled); resistant to welding sparks; 4 x 0.34 mm² (42 x Ø 0.1 mm)

Connection



EVW153



Connection cable

VDOAH043SCS02,5T04STGH040SCS

Electrical connection - Socket

Connector: 1 x M12, angled; coding: A; Moulded body: TPU (urethane), black transparent; Locking: brass, weld coated; sealing: FKM; Contacts: gold-plated; Tightening torque: 0.6...1.5 Nm

