




Inductive sensor

IEB3002,5BPOG/AS-510-TPS

Article no longer available - archive entry

Alternative articles: IE5292

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	2.5
Housing	Threaded type
Dimensions [mm]	M8 x 1 / L = 50

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	15; (24 V)
Reverse polarity protection	no

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	1
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	2000
Short-circuit protection	no
Overload protection	no

Monitoring range

Sensing range [mm]	2.5
Real sensing range Sr [mm]	2.5 ± 10 %
Operating distance [mm]	2.03

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2
Hysteresis [% of Sr]	1...15
Switch-point drift [% of Sr]	-10...10

Operating conditions

Ambient temperature [°C]	0...60
--------------------------	--------

IE5245



Inductive sensor

IEB3002,5BPOG/AS-510-TPS

Protection	IP 65
------------	-------

Mechanical data

Housing	Threaded type
Mounting	non-flush mountable
Dimensions [mm]	M8 x 1 / L = 50
Thread designation	M8 x 1
Material	housing: brass nickel-plated; sensing face: PBT

Displays / operating elements

Display	Switching status	1 x LED, yellow
---------	------------------	-----------------

Accessories


Items supplied	lock nuts: 2
----------------	--------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Connector: 1 x M8; coding: A



Connection

