




Inductive tube sensor

I8-3020-ANKG/DY/0,09M/US100DPS

Article no longer available - archive entry



Product characteristics

Electrical design	NPN
Output function	normally open
Sensing range [mm]	< 20
Housing	rectangular
Dimensions [mm]	70 x 20 x 12

Application

Principle of operation	dynamic
------------------------	---------

Electrical data

Operating voltage [V]	10...35 DC
Current consumption [mA]	< 25
Protection class	III
Reverse polarity protection	yes

Outputs

Electrical design	NPN
Output function	normally open
Max. voltage drop switching output DC [V]	2
Permanent current rating of switching output DC [mA]	200



Inductive tube sensor

I8-3020-ANKG/DY/0,09M/US100DPS

Short-circuit protection	yes
Overload protection	yes

Monitoring range

Sensing range	[mm]	< 20
Resolution of steel ball (diameter)	[mm]	1
Max. part speed	[m/s]	35

Reaction times

Pulse stretching	[ms]	100
Max. fall time	[ms]	100
Response time	[ms]	< 0.2

Operating conditions

Ambient temperature	[°C]	-25...70
Protection		IP 67

Mechanical data

Weight	[g]	38.2
Housing		rectangular
Dimensions	[mm]	70 x 20 x 12
Material		housing: PC

Displays / operating elements

Display	Switching status	1 x LED, yellow
	Power	1 x LED, green

Accessories

Items supplied	fixing straps: 2
----------------	------------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Cable: 0.09 m, PUR

Connector: 1 x M12; coding: A





Inductive tube sensor

I8-3020-ANKG/DY/0,09M/US100DPS

Connection

