




Inductive sensor

IA-2010-ABOW/ 6mPPU

Article no longer available - archive entry



Product characteristics

Output function		normally open
Sensing range	[mm]	10
Housing		tubular
Dimensions	[mm]	Ø 20

Electrical data

Frequency AC	[Hz]	47...63
Operating voltage	[V]	20...250 AC
Protection class		II
Reverse polarity protection		no

Outputs

Output function		normally open
Max. voltage drop switching output AC	[V]	5.5
Minimum load current	[mA]	5
Max. leakage current	[mA]	2.5
Permanent current rating of switching output AC	[mA]	300; (500 (...50 °C))
Short-time current rating of switching output	[mA]	2200; (20 ms / 0,5 Hz)
Switching frequency AC	[Hz]	20
Short-circuit protection		no
Overload protection		no

Monitoring range

Sensing range	[mm]	10
---------------	------	----



Inductive sensor

IA-2010-ABOW/ 6mPPU

Real sensing range Sr	[mm]	10 ± 10 %
Operating distance	[mm]	0...8.1

Accuracy / deviations

Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2
Hysteresis	[% of Sr]	1...15
Switch-point drift	[% of Sr]	-10...10

Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 67

Mechanical data

Housing		tubular
Mounting		non-flush mountable
Dimensions	[mm]	Ø 20
Material		PBT

Displays / operating elements

Display	Switching status	1 x LED, yellow
---------	------------------	-----------------

Accessories

Items supplied	Mounting clamp: 1
----------------	-------------------


Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 6 m, PUR / PVC; 2 x 0.5 mm²

Connection



BN = Core colors :
brown
BU = blue