



## Inductive sensor

IEB3006-APKG/V4A/AS



## Product characteristics

|                    |                 |
|--------------------|-----------------|
| Electrical design  | PNP             |
| Output function    | normally closed |
| Sensing range [mm] | 6               |
| Housing            | Threaded type   |
| Dimensions [mm]    | M8 x 1 / L = 30 |

## Application

|             |                                                                                                |
|-------------|------------------------------------------------------------------------------------------------|
| System      | gold-plated contacts; Increased sensing range                                                  |
| Application | Suitable for industrial, mobile, cooling and lubricating applications; Industrial applications |

## Electrical data

|                             |            |
|-----------------------------|------------|
| Operating voltage [V]       | 10...30 DC |
| Current consumption [mA]    | < 20       |
| Protection class            | III        |
| Reverse polarity protection | yes        |

## Outputs

|                                                      |                 |
|------------------------------------------------------|-----------------|
| Electrical design                                    | PNP             |
| Output function                                      | normally closed |
| Max. voltage drop switching output DC [V]            | 2.5             |
| Permanent current rating of switching output DC [mA] | 100             |
| Switching frequency DC [Hz]                          | 800             |
| Short-circuit protection                             | yes             |
| Overload protection                                  | yes             |

## Monitoring range

|                            |          |
|----------------------------|----------|
| Sensing range [mm]         | 6        |
| Real sensing range Sr [mm] | 6 ± 10 % |
| Operating distance [mm]    | 0...4.86 |
| Increased sensing range    | yes      |

## Accuracy / deviations

|                      |                                                                            |
|----------------------|----------------------------------------------------------------------------|
| Correction factor    | steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.5 / copper: 0.4 |
| Hysteresis [% of Sr] | 1...15                                                                     |

# IES218



## Inductive sensor

IEB3006-APKG/V4A/AS

|                    |           |          |
|--------------------|-----------|----------|
| Switch-point drift | [% of Sr] | -10...10 |
|--------------------|-----------|----------|

### Operating conditions

|                     |                                                                       |          |
|---------------------|-----------------------------------------------------------------------|----------|
| Ambient temperature | [°C]                                                                  | -40...85 |
| Protection          | IP 65; IP 66; IP 67; IP 68; IP 69K; (with ifm socket duly screwed on) |          |

### Tests / approvals

|                             |                           |                                                                                    |
|-----------------------------|---------------------------|------------------------------------------------------------------------------------|
| EMC                         | EN 61000-4-2 ESD          | 4 kV CD / 8 kV AD                                                                  |
|                             | EN 61000-4-3 HF radiated  | 10 V/m                                                                             |
|                             | EN 61000-4-4 Burst        | 2 kV                                                                               |
|                             | EN 61000-4-6 HF conducted | 10 V                                                                               |
|                             | EN 55011                  | class B                                                                            |
| Vibration resistance        | EN 60068-2-6 Fc           | 20 g (10...3000 Hz) / 50 sweep cycles per frequency; 1 octave per minute in 3 axes |
| Shock resistance            | EN 60068-2-27 Ea          | 100 g 11 ms half-sine; 3 shocks each in every direction of the 3 coordinate axes   |
| Continuous shock resistance | EN 60068-2-27             | 40 g 6 ms; 4000 shocks each in every direction of the 3 coordinate axes            |
| Fast temperature changes    | EN 60068-2-14 Na          | TA = -40 °C; TB = 85 °C; t1 = 30 min; t2 = < 10 s; 50 cycles                       |
| Salt spray test             | EN 60068-2-52 Kb          | severity level 5 (4 test cycles)                                                   |
| MTTF                        | [years]                   | 1443                                                                               |
| Embedded software included  |                           | yes                                                                                |
| UL approval                 | Ta                        | -25...80 °C                                                                        |
|                             | Enclosure type            | Type 1                                                                             |
|                             | voltage supply            | Limited Voltage/Current                                                            |
|                             | UL approval number        | A017                                                                               |
|                             | File number UL            | E174191                                                                            |

### Mechanical data

|                    |      |                                                                                                                          |
|--------------------|------|--------------------------------------------------------------------------------------------------------------------------|
| Weight             | [g]  | 16                                                                                                                       |
| Housing            |      | Threaded type                                                                                                            |
| Mounting           |      | non-flush mountable                                                                                                      |
| Dimensions         | [mm] | M8 x 1 / L = 30                                                                                                          |
| Thread designation |      | M8 x 1                                                                                                                   |
| Material           |      | stainless steel (1.4404 / 316L); sensing face: LCP white;<br>LED window: PEI; lock nuts: stainless steel (1.4404 / 316L) |
| Tightening torque  | [Nm] | A = 5 mm: 2 Nm; B: 5 Nm                                                                                                  |

### Displays / operating elements

|         |                  |                     |
|---------|------------------|---------------------|
| Display | Switching status | 4 x 90° LED, yellow |
|---------|------------------|---------------------|

### Accessories

|                |              |
|----------------|--------------|
| Items supplied | lock nuts: 2 |
|----------------|--------------|

### Remarks

|               |        |
|---------------|--------|
| Pack quantity | 1 pcs. |
|---------------|--------|

# IES218



## Inductive sensor


IEB3006-APKG/V4A/AS

### Electrical connection - plug

Connector: 1 x M8; coding: A; Contacts: gold-plated



### Connection



### Diagrams and graphs

#### Installation

