


# IA5082



## Inductive sensor

IA-3010-BPKG



### Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	10
Housing	tubular
Dimensions [mm]	Ø 20 / L = 77

### Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	15; (24 V)
Protection class	II
Reverse polarity protection	yes

### Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	300
Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)
Overload protection	yes

### Monitoring range

Sensing range [mm]	10
Real sensing range Sr [mm]	10 ± 10 %
Operating distance [mm]	0...8.1

### Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2
Hysteresis [% of Sr]	1...15
Switch-point drift [% of Sr]	-10...10

### Operating conditions

Ambient temperature [°C]	-25...80
Protection	IP 67


# IA5082



## Inductive sensor

IA-3010-BPKG

Tests / approvals		
EMC	EN 60947-5-2	
MTTF	[years]	1853
Mechanical data		
Weight	[g]	160.7
Housing		tubular
Mounting		non-flush mountable
Dimensions	[mm]	Ø 20 / L = 77
Material		housing: PBT
Displays / operating elements		
Display	Switching status	1 x LED, yellow
Accessories		
Items supplied		Mounting clamp: 1
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 2 m, PVC; 3 x 0.5 mm <sup>2</sup>		
Connection		



Core colors :  
BN = brown  
BU = blue  
BK = black