




## Inductive sensor

IB-2020-BBOW/ 6m

Article no longer available - archive entry



## Product characteristics

Output function		normally closed
Sensing range	[mm]	20
Housing		tubular
Dimensions	[mm]	Ø 34 / L = 82

## Electrical data

Frequency AC	[Hz]	47...63
Operating voltage	[V]	20...250 AC
Reverse polarity protection		no

## Outputs

Output function		normally closed
Max. voltage drop switching output AC	[V]	5.5
Minimum load current	[mA]	5
Max. leakage current	[mA]	2.5
Permanent current rating of switching output AC	[mA]	300; (500 (...50 °C))
Short-time current rating of switching output	[mA]	2200; (20 ms / 0,5 Hz)
Switching frequency AC	[Hz]	15
Short-circuit protection		no
Overload protection		no

## Monitoring range

Sensing range	[mm]	20
Real sensing range Sr	[mm]	20 ± 10 %
Operating distance	[mm]	0...16.2

## Accuracy / deviations

Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.4 / copper: 0.3
Hysteresis	[% of Sr]	1...15
Switch-point drift	[% of Sr]	-10...10

## Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 67

# IB0008



## Inductive sensor

IB-2020-BBOW/ 6m

### Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

### Mechanical data

Housing	tubular
Mounting	non-flush mountable
Dimensions [mm]	Ø 34 / L = 82
Material	PBT

### Displays / operating elements

Display	Switching status	1 x LED, yellow
---------	------------------	-----------------

### Accessories

Items supplied	Mounting clamp: 1
----------------	-------------------


### Remarks

Pack quantity	1 pcs.
---------------	--------

### Electrical connection

Cable: 6 m, PVC; 2 x 0.5 mm<sup>2</sup>

### Connection



BN = Core colors :  
brown  
BU = blue