




Inductive sensor

IFB2002-ABOW/ 5mPPU

Article no longer available - archive entry



Product characteristics

Output function		normally open
Sensing range	[mm]	2
Housing		Threaded type
Dimensions	[mm]	M12 x 1

Electrical data

Frequency AC	[Hz]	47...63
Operating voltage	[V]	80...250 AC
Protection class		II
Reverse polarity protection		yes

Outputs

Output function		normally open
Max. voltage drop switching output AC	[V]	11
Minimum load current	[mA]	5
Max. leakage current	[mA]	2.5
Permanent current rating of switching output AC	[mA]	200
Short-time current rating of switching output	[mA]	900; (20 ms / 0,5 Hz)
Switching frequency AC	[Hz]	25
Short-circuit protection		no
Overload protection		yes

Monitoring range

Sensing range	[mm]	2
---------------	------	---

IF0277



Inductive sensor

IFB2002-ABOW/ 5mPPU

Real sensing range Sr	[mm]	2 ± 10 %
Operating distance	[mm]	0...1.6

Accuracy / deviations		
Hysteresis	[% of Sr]	3...15
Switch-point drift	[% of Sr]	-15...15

Operating conditions		
Ambient temperature	[°C]	-25...70
Protection		IP 67

Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B


Mechanical data		
Housing		Threaded type
Mounting		flush mountable
Dimensions	[mm]	M12 x 1
Thread designation		M12 x 1
Material		brass chromium-plated; PBT

Displays / operating elements		
Display	Switching status	1 x LED, yellow

Accessories		
Items supplied		lock nuts: 2

Remarks		
Pack quantity		1 pcs.

Electrical connection		
Cable: 5 m, PUR; 2 x 0.5 mm²		
Connection		



BN = Core colors :
brown
BU = blue