


ID9200



Inductive sensor

IDE2040-ARKG

Article no longer available - archive entry



Product characteristics

Electrical design	PNP/NPN
Output function	normally open
Sensing range [mm]	40
Housing	rectangular
Dimensions [mm]	105 x 80 x 40

Electrical data

Operating voltage [V]	10...55 DC
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP/NPN
Output function	normally open
Max. voltage drop switching output DC [V]	4.5
Minimum load current [mA]	4
Max. leakage current [mA]	0.65 (55 V DC)
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	4
Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)
Overload protection	yes

ID9200



Inductive sensor

IDE2040-ARKG

Monitoring range		
Sensing range	[mm]	40
Sensing range adjustable		yes
Factory setting sensing range	[mm]	40
Real sensing range Sr	[mm]	$40 \pm 10 \%$
Operating distance	[mm]	0...40.5

Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2
Hysteresis	[% of Sr]	1...15
Switch-point drift	[% of Sr]	-10...10

Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 65

Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data		
Housing		rectangular
Mounting		non-flush mountable
Dimensions	[mm]	105 x 80 x 40
Material		PPE modified

Displays / operating elements		
Display	Switching status	1 x LED, yellow

Accessories		
Items supplied		screwdriver: 1

Remarks		
Pack quantity		1 pcs.

Electrical connection		
terminals: ...2.5 mm ² ; Cable sheath: Ø 7...13 mm		

Connection		
------------	--	--

