


IE5111

Inductive sensor

IEC3002-BNKG



Product characteristics

Electrical design	NPN
Output function	normally closed
Sensing range [mm]	2
Housing	Threaded type
Dimensions [mm]	M8 x 1 / L = 35

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	15; (24 V)
Protection class	III
Reverse polarity protection	yes

Outputs

Electrical design	NPN
Output function	normally closed
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	800
Short-circuit protection	yes
Overload protection	yes

Monitoring range

Sensing range [mm]	2
Real sensing range Sr [mm]	2 ± 10 %
Operating distance [mm]	0...1.6

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2
Hysteresis [% of Sr]	1...15
Switch-point drift [% of Sr]	-10...10

Operating conditions

Ambient temperature [°C]	-25...80
Protection	IP 67


IE5111



Inductive sensor

IEC3002-BNKG

Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	3 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	3 V
	EN 55011	class B
MTTF	[years]	5541
Mechanical data		
Weight	[g]	42.8
Housing		Threaded type
Mounting		non-flush mountable
Dimensions	[mm]	M8 x 1 / L = 35
Thread designation		M8 x 1
Material		PBT
Tightening torque	[Nm]	0.25
Displays / operating elements		
Display	Switching status	1 x LED, yellow
Accessories		
Items supplied		lock nuts: 2
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 2 m, PVC; 3 x 0.14 mm²		
Connection		



Core colors :
BN = brown
BU = blue
BK = black