
IE5161

Inductive sensor

IE-3001-APOG/10m

Article no longer available - archive entry



CE

Product characteristics		
Electrical design		PNP
Output function		normally closed
Sensing range	[mm]	1
Housing		Threaded type
Dimensions	[mm]	M8 x 1 / L = 50
Electrical data		
Operating voltage	[V]	10...36 DC
Current consumption	[mA]	15; (24 V)
Protection class		III
Reverse polarity protection		no
Outputs		
Electrical design		PNP
Output function		normally closed
Max. voltage drop switching output DC	[V]	1
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	1000
Short-circuit protection		no
Overload protection		no
Monitoring range		
Sensing range	[mm]	1
Real sensing range Sr	[mm]	1 ± 10 %
Operating distance	[mm]	0...0.8
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2
Hysteresis	[% of Sr]	1...15
Switch-point drift	[% of Sr]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67

IE5161


Inductive sensor

IE-3001-APOG/10m

Tests / approvals			
EMC		EN 60947-5-2	
		EN 55011	class B
MTTF	[years]	2737	
Mechanical data			
Housing		Threaded type	
Mounting		flush mountable	
Dimensions	[mm]	M8 x 1 / L = 50	
Thread designation		M8 x 1	
Material		PBT	
Displays / operating elements			
Display		Switching status	1 x LED, yellow
Accessories			
Items supplied		lock nuts: 2	
Remarks			
Pack quantity		1 pcs.	
Electrical connection			

Cable: 10 m, PVC; 3 x 0.14 mm²

Connection



	Core colors :
BN =	brown
BU =	blue
BK =	black