




Inductive sensor

IEC3002-ANOG/2,5m

Article no longer available - archive entry



Product characteristics

Electrical design	NPN
Output function	normally open
Sensing range [mm]	1
Housing	Threaded type
Dimensions [mm]	M8 x 1 / L = 35

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	10; (24 V)
Protection class	II
Reverse polarity protection	no

Outputs

Electrical design	NPN
Output function	normally open
Max. voltage drop switching output DC [V]	1
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	800
Short-circuit protection	no
Overload protection	no

Monitoring range

Sensing range [mm]	1
Real sensing range Sr [mm]	$1 \pm 10\%$
Operating distance [mm]	0...0.8

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.4 / copper: 0.3
Hysteresis [% of Sr]	1...15
Switch-point drift [% of Sr]	-10...10

Operating conditions

Ambient temperature [°C]	-25...80
Protection	IP 67

Mechanical data

Housing	Threaded type
---------	---------------

IE5171



Inductive sensor

IEC3002-ANOG/2,5m

Mounting	flush mountable
Dimensions [mm]	M8 x 1 / L = 35
Thread designation	M8 x 1
Material	PBT

Displays / operating elements

Display	Switching status	1 x LED, yellow
---------	------------------	-----------------

Accessories

Items supplied	lock nuts: 2
----------------	--------------


Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 2 m, PVC; 3 x 0.14 mm²

Connection



BN = Core colors : brown
BU = blue
BK = black