




Inductive sensor

IEB3002BBPKG/AS-610-TPS

Article no longer available - archive entry

Alternative articles: IE5338

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	2
Housing	Threaded type
Dimensions [mm]	M8 x 1

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	< 9.5
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	1.8
Permanent current rating of switching output DC [mA]	150
Switching frequency DC [Hz]	2000
Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)

IE5297



Inductive sensor

IEB3002BBPKG/AS-610-TPS

Overload protection	yes
---------------------	-----

Monitoring range

Sensing range	[mm]	2
Real sensing range Sr	[mm]	2 ± 10 %
Operating distance	[mm]	0...1.6

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2	
Hysteresis	[% of Sr]	1...15
Switch-point drift	[% of Sr]	-10...10

Operating conditions

Ambient temperature	[°C]	-25...70
Protection		IP 67

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data

Housing	Threaded type	
Mounting	flush mountable	
Dimensions	[mm]	M8 x 1
Thread designation	M8 x 1	
Material	PA 12-GF30; stainless steel (1.4305 / 303)	

Displays / operating elements

Display	Switching status	1 x LED, yellow
---------	------------------	-----------------

Accessories

Items supplied	lock nuts: 2
----------------	--------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Connector: 1 x M8; coding: A



IE5297



Inductive sensor

IEB3002BBPKG/AS-610-TPS

Connection

