


# IFC264



## Inductive full-metal sensor

IFK32,5BAPKG/AM/US-104/K0



### Product characteristics

Electrical design	PNP
Output function	normally closed
Sensing range [mm]	2.5
Housing	Threaded type
Dimensions [mm]	M12 x 1 / L = 60

### Application

Special feature	gold-plated contacts; Increased sensing range; Full-metal housing; correction factor = 0
Application	Oils and coolants
Media	Ferrous only; aluminum chip immune
Pressure rating	100 bar / 10 MPa
Note on pressure rating	sensing face

### Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	< 20
Protection class	III
Reverse polarity protection	yes

### Outputs

Electrical design	PNP
Output function	normally closed
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	100
Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)
Overload protection	yes

### Monitoring range


Sensing range [mm]	2.5
Operating distance [mm]	0...2.02
Increased sensing range	yes

# IFC264



## Inductive full-metal sensor

IFK32,5BAPKG/AM/US-104/K0

Accuracy / deviations		
Correction factor	steel: 1 / stainless steel: 0.5	
Correction factor = 0	yes	
Operating conditions		
Ambient temperature [°C]	-25...70	
Protection	IP 68; ("Coolant")	
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
	EN 55011	class B
Impact resistance	1 J	
MTTF [years]	1114	
Embedded software included	yes	
UL approval	Ta	-25...70 °C
	Enclosure type	Type 1
	voltage supply	Limited Voltage/Current
	UL approval number	A012
File number UL	E174191	
Mechanical data		
Weight [g]	28	
Housing	Threaded type	
Mounting	flush mountable	
Dimensions [mm]	M12 x 1 / L = 60	
Thread designation	M12 x 1	
Material	housing: stainless steel (1.4404 / 316L); sensing face: stainless steel (1.4404 / 316L); LED window: PEI; lock nuts: brass white bronze coated	
Tightening torque [Nm]	15	
Full-metal housing	yes	
Displays / operating elements		
Display	Switching status	4 x 90° LED, yellow
Accessories		
Items supplied	lock nuts: 2	
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
		


# IFC264



## Inductive full-metal sensor

IFK32,5BAPKG/AM/US-104/K0

### Connection



### Electrical connection - plug

Connector: 1 x M12; Contacts: gold-plated