




## Inductive full-metal sensor

IEK3002BBPKG/AM/US-104



## Product characteristics

Electrical design		PNP
Output function		normally open
Sensing range	[mm]	2
Housing		Threaded type
Dimensions	[mm]	M8 x 1 / L = 60

## Application

Special feature	gold-plated contacts; Increased sensing range; Full-metal housing	
Application	Oils and coolants	
Pressure rating	50 bar	10 MPa
Note on pressure rating	sensing face	

## Electrical data

Operating voltage	[V]	10...30 DC
Current consumption	[mA]	< 10
Protection class		III
Reverse polarity protection		yes

## Outputs

Electrical design		PNP
Output function		normally open
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	100
Short-circuit protection		yes
Overload protection		yes

## Monitoring range

Sensing range	[mm]	2
Real sensing range Sr	[mm]	2 ± 10 %
Operating distance	[mm]	0...1.62
Increased sensing range		yes

## Accuracy / deviations

Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.7 / aluminum: 0.6 / copper: 0.5
Hysteresis	[% of Sr]	1...20

# IEC200



## Inductive full-metal sensor

IEK3002BBPKG/AM/US-104

Switch-point drift	[% of Sr]	-10...10
--------------------	-----------	----------

### Operating conditions

Ambient temperature	[°C]	-25...70
---------------------	------	----------

Protection	IP 67; IP 68; IP 69K; ("Coolant")
------------	-----------------------------------

### Tests / approvals

EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
-----	------------------	-------------------

EN 61000-4-3 HF radiated	10 V/m
--------------------------	--------

EN 61000-4-4 Burst	2 kV
--------------------	------

EN 61000-4-6 HF conducted	10 V
---------------------------	------

EN 55011	class B
----------	---------

Impact resistance	1 J
-------------------	-----

MTTF	[years]	1446
------	---------	------

UL approval	Ta	-25...70 °C
-------------	----	-------------

Enclosure type	Type 1
----------------	--------

voltage supply	Limited Voltage/Current
----------------	-------------------------

UL approval number	A028
--------------------	------

File number UL	E174191
----------------	---------

### Mechanical data

Weight	[g]	21.4
--------	-----	------

Housing	Threaded type
---------	---------------

Mounting	flush mountable
----------	-----------------

Dimensions	[mm]	M8 x 1 / L = 60
------------	------	-----------------

Thread designation	M8 x 1
--------------------	--------

Material	stainless steel (1.4404 / 316L); sensing face: stainless steel (1.4404 / 316L); LED window: PEI; lock nuts: stainless steel (1.4404 / 316L)
----------	---

Tightening torque	[Nm]	< 5
-------------------	------	-----

Full-metal housing	yes
--------------------	-----

### Displays / operating elements

Display	Switching status	4 x 90° LED, yellow
---------	------------------	---------------------

### Accessories

Items supplied	lock nuts: 2
----------------	--------------

### Remarks

Pack quantity	1 pcs.
---------------	--------

### Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: gold-plated





## Inductive full-metal sensor

IEK3002BBPKG/AM/US-104

### Connection



### Diagrams and graphs

#### Installation

