




## Inductive full-metal sensor

IEB3002BANKG/AM/AS



Product characteristics	
Electrical design	NPN
Output function	normally open
Sensing range [mm]	2
Housing	Threaded type
Dimensions [mm]	M8 x 1 / L = 50
Application	
Special feature	gold-plated contacts; Increased sensing range
Application	Industrial applications; Oils and coolants
Pressure rating	50 bar   5 MPa
Note on pressure rating	sensing face
Electrical data	
Operating voltage [V]	10...30 DC
Current consumption [mA]	< 10
Protection class	III
Reverse polarity protection	yes
Outputs	
Electrical design	NPN
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	100
Short-circuit protection	yes
Overload protection	yes
Monitoring range	
Sensing range [mm]	2
Real sensing range Sr [mm]	2 ± 10 %
Operating distance [mm]	0...1.6
Increased sensing range	yes
Accuracy / deviations	
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.7 / aluminum: 0.6 / copper: 0.5
Hysteresis [% of Sr]	1...20

# IEC202



## Inductive full-metal sensor

IEB3002BANKG/AM/AS

Switch-point drift	[% of Sr]	-10...10
--------------------	-----------	----------

### Operating conditions

Ambient temperature	[°C]	-25...70
---------------------	------	----------

Protection	IP 65; IP 67; (with ifm socket duly screwed on)	
------------	---	--

### Tests / approvals

EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
	EN 55011	class B

Impact resistance		1 J
-------------------	--	-----

MTTF	[years]	1386
------	---------	------

Embedded software included	yes	
----------------------------	-----	--

UL approval	Ta	-25...70 °C
	Enclosure type	Type 1
	voltage supply	Limited Voltage/Current
	UL approval number	A017
	File number UL	E174191

### Mechanical data

Weight	[g]	18
--------	-----	----

Housing	Threaded type	
---------	---------------	--

Mounting	flush mountable	
----------	-----------------	--

Dimensions	[mm]	M8 x 1 / L = 50
------------	------	-----------------

Thread designation	M8 x 1	
--------------------	--------	--

Material	housing: stainless steel (1.4404 / 316L); sensing face: stainless steel (1.4404 / 316L); LED window: PPSU; lock nuts: stainless steel (1.4404 / 316L)	
----------	---	--

Tightening torque	[Nm]	< 5
-------------------	------	-----

### Displays / operating elements

Display	Switching status	4 LED, yellow
---------	------------------	---------------

### Accessories

Items supplied	lock nuts: 2	
----------------	--------------	--

### Remarks

Pack quantity	1 pcs.	
---------------	--------	--

### Electrical connection - plug

Connector: 1 x M8; coding: A; Contacts: 3, gold-plated



# IEC202



## Inductive full-metal sensor

IEB3002BANKG/AM/AS

### Connection

