

IF5448




Inductive sensor

IFK3004LANOG/V4A

Article no longer available - archive entry

Alternative articles: IF5492
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics		
Electrical design		NPN
Output function		normally open
Sensing range	[mm]	4
Housing		Threaded type
Dimensions	[mm]	M12 x 1
Electrical data		
Operating voltage	[V]	10...30 DC
Current consumption	[mA]	15; (24 V)
Protection class		II
Reverse polarity protection		no
Outputs		
Electrical design		NPN
Output function		normally open
Max. voltage drop switching output DC	[V]	1
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	300
Short-circuit protection		no

IF5448



Inductive sensor

IFK3004LANOG/V4A

Overload protection	no	
Monitoring range		
Sensing range	[mm]	4
Real sensing range Sr	[mm]	4 ± 10 %
Operating distance	[mm]	0...3.25
Accuracy / deviations		
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2	
Hysteresis	[% of Sr]	1...15
Switch-point drift	[% of Sr]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection	IP 67	
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Housing	Threaded type	
Mounting	non-flush mountable	
Dimensions	[mm]	M12 x 1
Thread designation	M12 x 1	
Material	stainless steel (1.4571/316Ti); PBT	
Displays / operating elements		
Display	Switching status	1 x LED, yellow
Accessories		
Items supplied	lock nuts: 2	
Remarks		
Pack quantity	1 pcs.	

IF5448



Inductive sensor

IFK3004LANOG/V4A

Electrical connection

Cable: 2 m, PVC; 3 x 0.14 mm²

Connection



	Core colors
BN	brown
BK	black
BU	blue