

IGA2005UARLA/SC/SL/LS-300BL



Output function		normally open
Sensing range	[mm]	5
Housing		Threaded type
Dimensions	[mm]	M18 x 1

System	Magnetic-field immune
Magnetic-field immune	yes

Frequency AC	[Hz]	47...63
Operating voltage	[V]	20...140 AC/DC
Protection class		I
Reverse polarity protection		no

Output function		normally open
Max. voltage drop switching output DC	[V]	5.5
Max. voltage drop switching output AC	[V]	5.5
Minimum load current	[mA]	5.5
Max. leakage current	[mA]	1.7 (140 V AC/DC)
Permanent current rating of switching output AC	[mA]	300



Inductive sensor

IGA2005UARLA/SC/SL/LS-300BL

Permanent current rating of switching output DC	[mA]	420
Short-time current rating of switching output	[mA]	420; (/ 300 AC (20ms / 0,5Hz))
Switching frequency AC	[Hz]	25
Switching frequency DC	[Hz]	500
Short-circuit protection		yes
Type of short-circuit protection		latching
Overload protection		no

Monitoring range		
Sensing range	[mm]	5
Real sensing range Sr	[mm]	5 ± 10 %
Operating distance	[mm]	0...4.05

Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2
Hysteresis	[% of Sr]	3...15
Switch-point drift	[% of Sr]	-10...10

Operating conditions		
Ambient temperature	[°C]	-25...70
Protection		IP 67

Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data		
Housing		Threaded type
Mounting		flush mountable
Dimensions	[mm]	M18 x 1
Thread designation		M18 x 1
Material		brass; PES; PTFE coated

Displays / operating elements		
Display	Switching status	1 x LED, red
	Power	1 x LED, green
	short circuit	1 x LED, green/red alternately flashing

Accessories		
Items supplied		lock nuts: 2

Remarks		
Pack quantity		1 pcs.

IG0318



Inductive sensor

IGA2005UARLA/SC/SL/LS-300BL

Electrical connection - plug

Connector: 1 x 7/8"; coding: A

