


Inductive sensor

IGA2008UARKA/SC/SL/LS-300BL

Article no longer available - archive entry



Product characteristics

Output function	normally open
Sensing range [mm]	8
Housing	Threaded type
Dimensions [mm]	M18 x 1

Application

System	Magnetic-field immune
Magnetic-field immune	yes

Electrical data

Frequency AC [Hz]	47...63
Operating voltage [V]	20...140 AC/DC
Protection class	I
Reverse polarity protection	no

Outputs

Output function	normally open
Max. voltage drop switching output DC [V]	5.5
Max. voltage drop switching output AC [V]	5.5
Minimum load current [mA]	5.5
Max. leakage current [mA]	1.7 (140 V AC/DC)
Permanent current rating of switching output AC [mA]	300



Inductive sensor

IGA2008UARKA/SC/SL/LS-300BL

Permanent current rating of switching output DC	[mA]	420
Switching frequency AC	[Hz]	25
Switching frequency DC	[Hz]	500
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes

Monitoring range

Sensing range	[mm]	8
Real sensing range Sr	[mm]	8 ± 10 %
Operating distance	[mm]	0...6.5

Accuracy / deviations

Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2
Hysteresis	[% of Sr]	3...15
Switch-point drift	[% of Sr]	-10...10

Operating conditions

Ambient temperature	[°C]	-25...70
Protection		IP 67

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data

Housing		Threaded type
Mounting		non-flush mountable
Dimensions	[mm]	M18 x 1
Thread designation		M18 x 1
Material		brass; sensing face: PC; PTFE coated

Displays / operating elements

Display	Switching status	1 x LED, red
	Power	1 x LED, green
	short circuit	1 x LED, green/red alternately flashing

Accessories

Items supplied		lock nuts: 2
----------------	--	--------------

Remarks

Pack quantity		1 pcs.
---------------	--	--------

IG0332



Inductive sensor

IGA2008UARKA/SC/SL/LS-300BL

Electrical connection - plug

Connector: 1 x 7/8"; coding: A

