

IG5678



Inductive sensor

IGA2005-FRKG/4M

Article no longer available - archive entry

Alternative articles: IG5620

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Electrical design	PNP/NPN
Output function	normally open / closed; (selectable)
Sensing range [mm]	5
Housing	Threaded type
Dimensions [mm]	M18 x 1 / L = 80

Electrical data

Operating voltage [V]	10...55 DC
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP/NPN
Output function	normally open / closed; (selectable)
Max. voltage drop switching output DC [V]	4.6
Minimum load current [mA]	4
Max. leakage current [mA]	0.8
Permanent current rating of switching output DC [mA]	400
Switching frequency DC [Hz]	700
Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)
Overload protection	yes

Monitoring range

Sensing range [mm]	5
Real sensing range S_r [mm]	$5 \pm 10 \%$
Operating distance [mm]	0...4.05

IG5678



Inductive sensor

IGA2005-FRKG/4M

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2	
Hysteresis [% of Sr]		1...15
Switch-point drift [% of Sr]		-10...10

Operating conditions

Ambient temperature [°C]	-25...80
Protection	IP 67

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B
MTTF [years]	1835	

Mechanical data

Weight [g]	0.245
Housing	Threaded type
Mounting	flush mountable
Dimensions [mm]	M18 x 1 / L = 80
Thread designation	M18 x 1
Material	brass white bronze coated; sensing face: PC

Displays / operating elements

Display	Switching status	1 x LED, yellow
---------	------------------	-----------------

Accessories

Items supplied	lock nuts: 2
----------------	--------------



Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 4 m, PUR / PVC; 2 x 0.5 mm²

Connection



Core colors :
BK = black
WH = white