




Inductive sensor

IGB2008BAROG/SC/UP/2LED/3M/VH

Article no longer available - archive entry

Alternative articles: IGS720

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Electrical design	PNP/NPN
Output function	normally open
Sensing range [mm]	8
Housing	Threaded type
Dimensions [mm]	M18 x 1 / L = 43

Application

System	Increased sensing range; optical setting aid; weld coated
--------	---

Electrical data

Operating voltage [V]	10...36 DC
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP/NPN
Output function	normally open
Max. voltage drop switching output DC [V]	5
Minimum load current [mA]	5
Max. leakage current [mA]	1
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	100
Short-circuit protection	no
Overload protection	no

Monitoring range

Sensing range [mm]	8
Operating distance [mm]	0...6.5
Increased sensing range	yes


IG5805



Inductive sensor

IGB2008BAROG/SC/UP/2LED/3M/VH

Accuracy / deviations		
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.4 / copper: 0.3	
Hysteresis [% of Sr]	3...15	
Operating conditions		
Ambient temperature [°C]	-25...70	
Protection	IP 67	
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Weight [g]	193	
Housing	Threaded type	
Mounting	flush mountable	
Dimensions [mm]	M18 x 1 / L = 43	
Thread designation	M18 x 1	
Material	housing: brass weld coated; sensing face: PBT weld coated; end cap: PC	
Displays / operating elements		
Display	Switching status	1 x LED, green
	Setting aid	1 x LED, red
Optical setting aid	yes	
Accessories		
Items supplied	lock nuts: 2	
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
Cable: 3 m, PVC; cross-linked; 2 x 0.5 mm²		
Connection		



BK = Core colors :
black