




Inductive sensor

IGB2012-AROG/UP/2LED/3M/PH

Article no longer available - archive entry

Alternative articles: IGS711

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Electrical design	PNP/NPN
Output function	normally open
Sensing range [mm]	12
Housing	Threaded type
Dimensions [mm]	M18 x 1

Application

System	Increased sensing range; optical setting aid
--------	--

Electrical data

Operating voltage [V]	10...36 DC
Protection class	II
Reverse polarity protection	no

Outputs

Electrical design	PNP/NPN
Output function	normally open
Max. voltage drop switching output DC [V]	5
Minimum load current [mA]	5
Max. leakage current [mA]	1
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	100
Short-circuit protection	no
Overload protection	no

Monitoring range


Sensing range [mm]	12
Increased sensing range	yes



Inductive sensor

IGB2012-AROG/UP/2LED/3M/PH

Accuracy / deviations		
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.5 / copper: 0.4	
Operating conditions		
Ambient temperature	[°C]	-25...70
Protection	IP 67	
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Weight	[g]	166.3
Housing	Threaded type	
Mounting	non-flush mountable	
Dimensions	[mm]	M18 x 1
Thread designation	M18 x 1	
Material	brass white bronze coated; PBT	
Displays / operating elements		
Display	Switching status	1 x LED, red
	Switching status	1 x LED, green
Optical setting aid	yes	
Accessories		
Items supplied	lock nuts: 2	
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
Cable: 3 m, PUR / PVC; 2 x 0.5 mm²		
Connection		



BK =

Core colors :
black