




## Inductive sensor

IGB3005-BNOG/20m

Article no longer available - archive entry



### Product characteristics

Electrical design	NPN
Output function	normally closed
Sensing range [mm]	5
Housing	Threaded type
Dimensions [mm]	M18 x 1 / L = 38

### Electrical data

Operating voltage [V]	18...36 DC
Current consumption [mA]	15; (24 V)
Protection class	II
Reverse polarity protection	no

### Outputs

Electrical design	NPN
Output function	normally closed
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	125; (150 (...50 °C))
Switching frequency DC [Hz]	500
Short-circuit protection	no
Overload protection	no

### Monitoring range

Sensing range [mm]	5
Real sensing range $S_r$ [mm]	$5 \pm 10 \%$
Operating distance [mm]	0...4.05

### Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2
Hysteresis [% of $S_r$ ]	1...15
Switch-point drift [% of $S_r$ ]	-10...10

### Operating conditions

Ambient temperature [°C]	-25...80
Protection	IP 67

# IG5253



## Inductive sensor

IGB3005-BNOG/20m

Mechanical data	
Housing	Threaded type
Mounting	flush mountable
Dimensions [mm]	M18 x 1 / L = 38
Thread designation	M18 x 1
Material	brass nickel-plated; PBT


Displays / operating elements		
Display	Switching status	1 x LED, yellow

Accessories	
Items supplied	lock nuts: 2

Remarks	
Pack quantity	1 pcs.

Electrical connection	
Cable: 20 m, PVC; 3 x 0.5 mm <sup>2</sup>	

Connection	
------------	--



	Core colors :
BN =	brown
BU =	blue
BK =	black