



## Inductive sensor

IG-3008-BNKG/10m

Article no longer available - archive entry



### Product characteristics

|                    |                  |
|--------------------|------------------|
| Electrical design  | NPN              |
| Output function    | normally closed  |
| Sensing range [mm] | 8                |
| Housing            | Threaded type    |
| Dimensions [mm]    | M18 x 1 / L = 80 |

### Electrical data

|                             |            |
|-----------------------------|------------|
| Operating voltage [V]       | 10...36 DC |
| Current consumption [mA]    | 15; (24 V) |
| Protection class            | II         |
| Reverse polarity protection | yes        |

### Outputs

|                                                      |                    |
|------------------------------------------------------|--------------------|
| Electrical design                                    | NPN                |
| Output function                                      | normally closed    |
| Max. voltage drop switching output DC [V]            | 2.5                |
| Permanent current rating of switching output DC [mA] | 250                |
| Switching frequency DC [Hz]                          | 300                |
| Short-circuit protection                             | yes                |
| Type of short-circuit protection                     | yes (non-latching) |
| Overload protection                                  | yes                |

### Monitoring range

|                            |          |
|----------------------------|----------|
| Sensing range [mm]         | 8        |
| Real sensing range Sr [mm] | 8 ± 10 % |
| Operating distance [mm]    | 0...6.5  |

### Accuracy / deviations

|                              |                                                                            |
|------------------------------|----------------------------------------------------------------------------|
| Correction factor            | steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2 |
| Hysteresis [% of Sr]         | 1...15                                                                     |
| Switch-point drift [% of Sr] | -10...10                                                                   |

# IG5391



## Inductive sensor

IG-3008-BNKG/10m

### Operating conditions

|                     |      |          |
|---------------------|------|----------|
| Ambient temperature | [°C] | -25...80 |
| Protection          |      | IP 67    |

### Tests / approvals

|     |              |  |
|-----|--------------|--|
| EMC | EN 60947-5-2 |  |
|-----|--------------|--|

### Mechanical data

|                    |      |                     |
|--------------------|------|---------------------|
| Housing            |      | Threaded type       |
| Mounting           |      | non-flush mountable |
| Dimensions         | [mm] | M18 x 1 / L = 80    |
| Thread designation |      | M18 x 1             |
| Material           |      | PBT                 |

### Displays / operating elements

|         |                  |                 |
|---------|------------------|-----------------|
| Display | Switching status | 1 x LED, yellow |
|---------|------------------|-----------------|

### Accessories

|                |  |              |
|----------------|--|--------------|
| Items supplied |  | lock nuts: 2 |
|----------------|--|--------------|


### Remarks

|               |  |        |
|---------------|--|--------|
| Pack quantity |  | 1 pcs. |
|---------------|--|--------|

### Electrical connection

Cable: 10 m, PVC; 3 x 0.5 mm<sup>2</sup>

#### Connection



Core colors :  
BN = brown  
BU = blue  
BK = black