

IFC223



Inductive sensor

IFG3004-BNKG/M/5V/3,1M/PH/

Article no longer available - archive entry



Product characteristics		
Electrical design		NPN
Output function		normally closed
Sensing range	[mm]	4
Housing		tubular
Dimensions	[mm]	Ø 12
Application		
Application		Oils and coolants
Electrical data		
Operating voltage tolerance	[%]	10
Operating voltage	[V]	5 DC
Current consumption	[mA]	< 15
Protection class		II
Reverse polarity protection		no
Outputs		
Electrical design		NPN
Output function		normally closed
Max. voltage drop switching output DC	[V]	0.4

IFC223



Inductive sensor

IFG3004-BNKG/M/5V/3,1M/PH/

Max. leakage current	[mA]	0.1
Permanent current rating of switching output DC	[mA]	10
Switching frequency DC	[Hz]	700
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes

Monitoring range		
Sensing range	[mm]	4
Operating distance	[mm]	0...3.25

Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.4 / copper: 0.3
Hysteresis	[% of Sr]	1...20

Operating conditions		
Ambient temperature	[°C]	-25...70
Protection		IP 68; ("Coolant")

Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
	EN 55011	class B

Mechanical data		
Housing		tubular
Mounting		non-flush mountable
Dimensions	[mm]	Ø 12
Material		sensing face: LCP; housing: stainless steel; Angle brackets: stainless steel; LED window: PEI

Displays / operating elements		
Display	Switching status	1 x LED, yellow

Remarks		
Pack quantity		1 pcs.

IFC223



Inductive sensor

IFG3004-BNKG/M/5V/3,1M/PH/

Electrical connection

Cable: 3.1 m, PUR / PVC; 3 x 0.34 mm²

Connection



	Core colors :
BK =	black
BN =	brown
BU =	blue