

IFC234



Inductive sensor

IFK2004BFRKG/2LED/US-104



Product characteristics

Electrical design	PNP/NPN
Output function	normally open / closed; (selectable)
Sensing range [mm]	4
Housing	Threaded type
Dimensions [mm]	M12 x 1 / L = 60

Application

System	gold-plated contacts; Increased sensing range; optical setting aid
Application	Oils and coolants

Electrical data

Operating voltage [V]	10...30 DC
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP/NPN
Output function	normally open / closed; (selectable)
Max. voltage drop switching output DC [V]	4.6
Minimum load current [mA]	4
Max. leakage current [mA]	1
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	700
Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)
Overload protection	yes

Monitoring range

Sensing range [mm]	4
Operating distance [mm]	0...3.25
Increased sensing range	yes



Inductive sensor

IFK2004BFRKG/2LED/US-104

Accuracy / deviations			
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.5 / copper: 0.4	
Hysteresis	[% of Sr]	1...15	
Operating conditions			
Ambient temperature		[°C]	-25...70
Protection		IP 68; ("Coolant")	
Tests / approvals			
EMC		EN 61000-4-2 ESD	4 kV CD / 8 kV AD
		EN 61000-4-3 HF radiated	10 V/m
		EN 61000-4-4 Burst	2 kV
		EN 61000-4-6 HF conducted	10 V
		EN 55011	class B
MTTF	[years]	1424	
Mechanical data			
Weight		[g]	27.7
Housing		Threaded type	
Mounting		flush mountable	
Dimensions		[mm]	M12 x 1 / L = 60
Thread designation		M12 x 1	
Material		housing: brass white bronze coated; sensing face: LCP white; LED window: PEI; lock nuts: brass white bronze coated	
Tightening torque		[Nm]	7
Displays / operating elements			
Display		Switching status	4 x 90° LED, yellow
		Setting aid	1 x LED, red
Optical setting aid		yes	
Accessories			
Items supplied		lock nuts: 2	
Remarks			
Pack quantity		1 pcs.	
Electrical connection - plug			
Connector: 1 x M12; coding: A; Contacts: gold-plated			
			

IFC234



Inductive sensor

IFK2004BFRKG/2LED/US-104

Connection

