


## Inductive sensor

IIA2010-BBOW/V4A/20m

Article no longer available - archive entry



## Product characteristics

Output function		normally closed
Sensing range	[mm]	10
Housing		Threaded type
Dimensions	[mm]	M30 x 1.5

## Electrical data

Frequency AC	[Hz]	47...63
Operating voltage	[V]	20...250 AC
Protection class		II
Reverse polarity protection		no

## Outputs

Output function		normally closed
Max. voltage drop switching output AC	[V]	5.5
Minimum load current	[mA]	5
Max. leakage current	[mA]	2.5
Permanent current rating of switching output AC	[mA]	300; (500 (...50 °C))
Short-time current rating of switching output	[mA]	2200; (20 ms / 0,5 Hz)
Switching frequency AC	[Hz]	20
Short-circuit protection		no
Overload protection		no

## Monitoring range

Sensing range	[mm]	10
---------------	------	----

**Inductive sensor**

IIA2010-BBOW/V4A/20m

Real sensing range Sr	[mm]	10 ± 10 %
Operating distance	[mm]	0...8.1

**Accuracy / deviations**

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2	
Hysteresis	[% of Sr]	1...15
Switch-point drift	[% of Sr]	-10...10

**Operating conditions**

Ambient temperature	[°C]	-25...80
Protection		IP 67

**Mechanical data**

Housing		Threaded type
Mounting		flush mountable
Dimensions	[mm]	M30 x 1.5
Thread designation		M30 x 1.5
Material		stainless steel (1.4571/316Ti); PBT

**Displays / operating elements**


Display	Switching status	1 x LED, yellow
---------	------------------	-----------------

**Accessories**

Items supplied	lock nuts: 2
----------------	--------------

**Remarks**

Pack quantity	1 pcs.
---------------	--------

**Electrical connection**Cable: 20 m, PVC; 2 x 0.5 mm<sup>2</sup>**Connection**

BN =  
BU =

Core colors :  
brown  
blue