


Inductive sensor

IGK2012-ABOA/0,98M/PH/LS100AKR

Article no longer available - archive entry



Product characteristics

Output function		normally open
Sensing range	[mm]	12
Housing		Threaded type
Dimensions	[mm]	M18 x 1

Application

System	Increased sensing range
--------	-------------------------

Electrical data

Operating voltage	[V]	20...250 AC/DC
Protection class		II
Reverse polarity protection		no

Outputs

Output function		normally open
Max. voltage drop switching output DC	[V]	6
Max. voltage drop switching output AC	[V]	6.5
Minimum load current	[mA]	5
Max. leakage current	[mA]	2.5 (250 V AC) / 1.3 (110 V AC) / 0.8 (24 V DC)
Permanent current rating of switching output AC	[mA]	250; (350 (...50 °C))
Permanent current rating of switching output DC	[mA]	100



Inductive sensor

IGK2012-ABOA/0,98M/PH/LS100AKR

Short-time current rating of switching output	[mA]	2200; (20 ms / 0,5 Hz)
Switching frequency AC	[Hz]	25
Switching frequency DC	[Hz]	50
Short-circuit protection		no
Overload protection		no

Monitoring range		
Sensing range	[mm]	12
Real sensing range Sr	[mm]	20 ± 10 %
Operating distance	[mm]	0...9.7
Increased sensing range		yes

Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.4 / copper: 0.3
Hysteresis	[% of Sr]	3...15
Switch-point drift	[% of Sr]	-10...10

Operating conditions		
Ambient temperature	[°C]	-25...70
Protection		IP 67

Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data		
Housing		Threaded type
Mounting		non-flush mountable
Dimensions	[mm]	M18 x 1
Thread designation		M18 x 1
Material		brass white bronze coated; PBT

Displays / operating elements		
Display	Switching status	1 x LED, red

Accessories		
Items supplied		lock nuts: 2

Remarks		
Pack quantity		1 pcs.

IG0393



Inductive sensor

IGK2012-ABOA/0,98M/PH/LS100AKR

Electrical connection - plug

Cable: 0.98 m, PUR; 2 x 0.5 mm²

Connector: 1 x 1/2"; coding: C

