




Inductive sensor

IIA2010-FRKG/V4A/US-100-IRF/AU



Product characteristics		
Electrical design		PNP/NPN
Output function		normally open / closed; (selectable)
Sensing range	[mm]	10
Housing		Threaded type
Dimensions	[mm]	M30 x 1.5 / L = 92
Application		
System		gold-plated contacts
Application		Industrial applications
Electrical data		
Operating voltage	[V]	10...55 DC
Protection class		II
Reverse polarity protection		yes
Outputs		
Electrical design		PNP/NPN
Output function		normally open / closed; (selectable)
Max. voltage drop switching output DC	[V]	4.6
Minimum load current	[mA]	4
Max. leakage current	[mA]	0.8
Permanent current rating of switching output DC	[mA]	400
Switching frequency DC	[Hz]	450
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes
Monitoring range		
Sensing range	[mm]	10
Real sensing range Sr	[mm]	10 ± 10 %

II5751



Inductive sensor

IIA2010-FRKG/V4A/US-100-IRF/AU

Operating distance	[mm]	0...8.1
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.4 / copper: 0.3
Hysteresis	[% of Sr]	3...15
Switch-point drift	[% of Sr]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
MTTF	[years]	1835
Mechanical data		
Weight	[g]	160
Housing		Threaded type
Mounting		flush mountable
Dimensions	[mm]	M30 x 1.5 / L = 92
Thread designation		M30 x 1.5
Material		stainless steel (1.4571/316Ti); sensing face: PC
Displays / operating elements		
Display	Switching status	1 x LED, yellow
Accessories		
Items supplied		lock nuts: 2
Remarks		
Pack quantity		1 pcs.

II5751



Inductive sensor

IIA2010-FRKG/V4A/US-100-IRF/AU

Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: gold-plated

