




## Inductive sensor

IIB3015-APOG

Article no longer available - archive entry

Alternative articles: II5456

When selecting an alternative article and accessories please note that technical data may differ!



## Product characteristics

Electrical design	PNP
Output function	normally closed
Sensing range [mm]	15
Housing	Threaded type
Dimensions [mm]	M30 x 1.5 / L = 45

## Electrical data

Operating voltage [V]	18...36 DC
Current consumption [mA]	7; (24 V)
Protection class	II
Reverse polarity protection	yes

## Outputs

Electrical design	PNP
Output function	normally closed
Max. voltage drop switching output DC [V]	2
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	250
Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)
Overload protection	yes

## Monitoring range


Sensing range [mm]	15
Real sensing range Sr [mm]	15 ± 10 %
Operating distance [mm]	0...12.1



## Inductive sensor

IIB3015-APOG

Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2
Hysteresis	[% of Sr]	
Switch-point drift	[% of Sr]	
		1...15
		-10...10
Operating conditions		
Ambient temperature		[-°C]
Protection		IP 67
Mechanical data		
Housing		Threaded type
Mounting		non-flush mountable
Dimensions		[mm]
Thread designation		M30 x 1.5 / L = 45
Material		M30 x 1.5
		brass nickel-plated; PBT
Displays / operating elements		
Display		Switching status
		1 x LED, yellow
Accessories		
Items supplied		lock nuts: 2
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 2 m, PVC; 3 x 0.5 mm²		
Connection		



Core colors :

BN = brown

BU = blue

BK = black