


IL5021



Inductive sensor

ILA32,5-BPKG/OBEN/AS514TPS RT



1 sensing face



Product characteristics		
Electrical design		PNP
Output function		normally open
Sensing range	[mm]	2.5
Housing		rectangular
Dimensions	[mm]	40 x 8 x 8
Electrical data		
Operating voltage	[V]	10...36 DC
Current consumption	[mA]	15; (24 V)
Protection class		III
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		normally open
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	2000
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes
Monitoring range		
Sensing range	[mm]	2.5
Real sensing range Sr	[mm]	2.5 ± 10 %

IL5021



Inductive sensor

ILA32,5-BPKG/OBEN/AS514TPS RT

Operating distance	[mm]	0...2.02
--------------------	------	----------

Accuracy / deviations

Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.4 / copper: 0.3
Hysteresis	[% of Sr]	1...15
Switch-point drift	[% of Sr]	-10...10

Operating conditions

Ambient temperature	[°C]	-25...70
Protection		IP 65

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B
MTTF	[years]	3449
UL approval	Ta	-25...70 °C
	Enclosure type	Type 1
	voltage supply	Limited Voltage/Current
	File number UL	E174191

Mechanical data

Weight	[g]	13.5
Housing		rectangular
Mounting		flush mountable
Dimensions	[mm]	40 x 8 x 8
Material		brass white bronze coated; LCP
Tightening torque	[Nm]	1; (insertion depth: > 5 mm)

Displays / operating elements

Display	Switching status	4 x 90° LED, red
---------	------------------	------------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Connector: 1 x M8; coding: A



IL5021



Inductive sensor

ILA32,5-BPKG/OBEN/AS514TPS RT

Connection

