




Inductive sensor

IMC2035-ARKA/LS-100AK



Product characteristics

Output function	normally open
Sensing range [mm]	35
Housing	rectangular

Application

System	Increased sensing range
--------	-------------------------

Electrical data

Frequency AC [Hz]	47...63
Operating voltage [V]	20...140 AC / 10...140 DC
Protection class	I
Reverse polarity protection	yes

Outputs

Output function	normally open
Max. voltage drop switching output DC [V]	5.5
Max. voltage drop switching output AC [V]	5.5
Minimum load current [mA]	5.5
Max. leakage current [mA]	1.7 (140 V AC/DC)
Short-time current rating of switching output [mA]	2200; (20 ms / 0,5 Hz)
Switching frequency AC [Hz]	25
Switching frequency DC [Hz]	100

IM0041



Inductive sensor

IMC2035-ARKA/LS-100AK

Short-circuit protection		yes	
Type of short-circuit protection		yes (non-latching)	
Overload protection		yes	
Monitoring range			
Sensing range		[mm]	35
Operating distance		[mm]	0...28.3
Increased sensing range		yes	
Accuracy / deviations			
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.4 / copper: 0.3	
Hysteresis		[% of Sr]	3...15
Operating conditions			
Ambient temperature		[°C]	-25...70
Protection		IP 67	
Tests / approvals			
EMC		EN 60947-5-2	
MTTF		[years]	353
UL approval		Ta	0...40 °C
		Enclosure type	Type 1
		voltage supply	Hazardous voltage
		File number UL	E174191
Mechanical data			
Weight		[g]	254.55
Housing		rectangular	
Mounting		non-flush mountable	
Material		PPE; clamp: diecast zinc	
Displays / operating elements			
Display		Switching status	1 x LED, red
		Power	1 x LED, green
Remarks			
Remarks		5 positions of the active zone possible	
Pack quantity		1 pcs.	

IM0041



Inductive sensor

IMC2035-ARKA/LS-100AK

Electrical connection - plug

Connector: 1 x 1/2"; coding: C; Locking: brass

