


IM5070



Inductive sensor

IMC3035ZBPKG/US-100-DPS

Article no longer available - archive entry



Product characteristics		
Electrical design		PNP
Output function		normally open
Sensing range	[mm]	35
Housing		rectangular
Dimensions	[mm]	40 x 40 x 66
Application		
System		gold-plated contacts
Electrical data		
Operating voltage	[V]	10...36 DC
Current consumption	[mA]	15; (24 V)
Protection class		II
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		normally open

IM5070



Inductive sensor

IMC3035ZBPKG/US-100-DPS

Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	100
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes

Monitoring range		
Sensing range	[mm]	35

Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.4 / copper: 0.3

Operating conditions		
Ambient temperature	[°C]	0...100
Protection		IP 67

Tests / approvals		
EMC	EN 60947-5-2	

Mechanical data		
Housing		rectangular
Mounting		non-flush mountable
Dimensions	[mm]	40 x 40 x 66
Material		housing: PPE; sensing face: PPE; end cap: PPS; clamp: PPS

Displays / operating elements		
Display	Switching status	1 x LED, yellow
	Power	1 x LED, green

Accessories		
Items supplied		Mounting bracket: 1
		Allen key: 1

Remarks		
Remarks		5 positions of the active zone possible
Pack quantity		1 pcs.

Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: gold-plated



IM5070



Inductive sensor

IMC3035ZBPKG/US-100-DPS

Connection

