

II5457




Inductive sensor

IIB3015-ANKG/US-100-DNS

Article no longer available - archive entry

Alternative articles: II5292 + E11504
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Electrical design	NPN
Output function	normally open
Sensing range [mm]	15
Housing	Threaded type
Dimensions [mm]	M30 x 1.5

Electrical data

Operating voltage [V]	18...36 DC
Current consumption [mA]	15; (24 V)
Reverse polarity protection	no

Outputs

Electrical design	NPN
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	125; (150 (...50 °C))
Switching frequency DC [Hz]	250
Short-circuit protection	yes



Inductive sensor

IIB3015-ANKG/US-100-DNS

Type of short-circuit protection	yes (non-latching)
Overload protection	yes

Monitoring range	
Sensing range [mm]	15
Real sensing range S_r [mm]	$15 \pm 10 \%$
Operating distance [mm]	0...12.1

Accuracy / deviations	
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2
Hysteresis [% of S_r]	1...15
Switch-point drift [% of S_r]	-10...10

Operating conditions	
Ambient temperature [°C]	-25...80
Protection	IP 65

Mechanical data	
Housing	Threaded type
Mounting	non-flush mountable
Dimensions [mm]	M30 x 1.5
Thread designation	M30 x 1.5
Material	brass nickel-plated; PBT

Displays / operating elements		
Display	Switching status	1 x LED, yellow

Accessories	
Items supplied	lock nuts: 2

Remarks	
Pack quantity	1 pcs.

Electrical connection - plug

Connector: 1 x M12; coding: A



II5457

Inductive sensor

IIB3015-ANKG/US-100-DNS



Connection

