


IM5127



Inductive sensor

IMC2015-ARKG/UP/US-100-DRS



Product characteristics		
Electrical design		PNP/NPN
Output function		normally open
Sensing range	[mm]	15
Housing		rectangular
Dimensions	[mm]	40 x 40 x 54
Electrical data		
Operating voltage	[V]	10...36 DC
Protection class		II
Reverse polarity protection		yes
Outputs		
Electrical design		PNP/NPN
Output function		normally open
Max. voltage drop switching output DC	[V]	4.6
Minimum load current	[mA]	2
Max. leakage current	[mA]	0.8
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	200

IM5127



Inductive sensor

IMC2015-ARKG/UP/US-100-DRS

Short-circuit protection		yes	
Type of short-circuit protection		yes (non-latching)	
Overload protection		yes	
Monitoring range			
Sensing range	[mm]	15	
Real sensing range Sr	[mm]	15 ± 10 %	
Operating distance	[mm]	0...12.1	
Accuracy / deviations			
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.4 / copper: 0.3	
Hysteresis	[% of Sr]	1...15	
Switch-point drift	[% of Sr]	-10...10	
Operating conditions			
Ambient temperature	[°C]	-25...70	
Protection		IP 67	
Tests / approvals			
EMC	EN 61000-4-2 ESD		8 kV CD / 6 kV AD
	EN 61000-4-3 HF radiated		10 V/m
	EN 61000-4-4 Burst		2 kV
	EN 61000-4-5 Surge		0,5 kV line to line, Ri: 2 Ohm
	EN 61000-4-6 HF conducted		10 V
	EN 55011		class B
MTTF	[years]	1740	
Mechanical data			
Weight	[g]	143.5	
Housing		rectangular	
Sensing face		5 positions selectable	
Mounting		flush mountable	
Dimensions	[mm]	40 x 40 x 54	
Material		PA	
Displays / operating elements			
Display		Switching status	1 x LED, yellow
Remarks			
Pack quantity		1 pcs.	

IM5127



Inductive sensor

IMC2015-ARKG/UP/US-100-DRS

Electrical connection - plug

Connector: 1 x M12; coding: A; Locking: locking, rotatable

