


IN5412



Inductive sensor

INV3004DBPKG/US

Article no longer available - archive entry



- 1 sensor 1
- 2 sensor 2
- 3 LED OUT 1
- 4 LED OUT21



Product characteristics	
Electrical design	PNP
Output function	2 x normally open
Sensing range [mm]	4
Housing	rectangular
Dimensions [mm]	33 x 60 x 64
Electrical data	
Operating voltage [V]	10...30 DC; (; to PELV)
Current consumption [mA]	15; (a maximum of one output is switched)
Protection class	III
Reverse polarity protection	yes
Outputs	
Electrical design	PNP
Output function	2 x normally open

IN5412



Inductive sensor

INV3004DBPKG/US

Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	500
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes

Monitoring range		
Sensing range	[mm]	4
Real sensing range Sr	[mm]	4 ± 10 %
Operating distance	[mm]	0...3.25

Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.4 / copper: 0.3
Hysteresis	[% of Sr]	1...15
Switch-point drift	[% of Sr]	-10...10

Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67

Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data		
Housing		rectangular
Mounting		non-flush mountable
Dimensions	[mm]	33 x 60 x 64
Material		housing: PA; screws: stainless steel; washer: stainless steel

Displays / operating elements		
Display	Switching status	2 x LED, yellow

Accessories		
Items supplied		washers: 2
		cylinder screws: 2 x M5 x 18

Remarks		
Pack quantity		1 pcs.

Electrical connection - plug

Connector: 1 x M12; coding: A



IN5412



Inductive sensor

INV3004DBPKG/US

Connection

