




Inductive sensor

IIB2012BAROG/UP/2LED/3M/PH

Article no longer available - archive entry

Alternative articles: IIS717

When selecting an alternative article and accessories please note that technical data may differ!



1 LED 2 x



Product characteristics

Electrical design	PNP/NPN
Output function	normally open
Sensing range [mm]	12
Housing	Threaded type
Dimensions [mm]	M30 x 1.5 / L = 44

Application

System	Increased sensing range; optical setting aid
--------	--

Electrical data

Operating voltage [V]	10...36 DC
Protection class	II
Reverse polarity protection	no

Outputs

Electrical design	PNP/NPN
Output function	normally open
Max. voltage drop switching output DC [V]	5
Minimum load current [mA]	5
Max. leakage current [mA]	1
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	100
Short-circuit protection	no
Overload protection	no



Inductive sensor

IIB2012BAROG/UP/2LED/3M/PH

Monitoring range		
Sensing range	[mm]	12
Operating distance	[mm]	0...9.7
Increased sensing range		yes
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.5 / copper: 0.4
Hysteresis	[% of Sr]	1...15
Operating conditions		
Ambient temperature	[°C]	-25...70
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Weight	[g]	256
Housing		Threaded type
Mounting		flush mountable
Dimensions	[mm]	M30 x 1.5 / L = 44
Thread designation		M30 x 1.5
Material		brass white bronze coated; PBT
Displays / operating elements		
Display	Switching status	1 x LED, red
	Switching status	1 x LED, green
Optical setting aid		yes
Accessories		
Items supplied		lock nuts: 2
Remarks		
Pack quantity		1 pcs.

II5709



Inductive sensor

IIB2012BAROG/UP/2LED/3M/PH

Electrical connection

Cable: 3 m, PUR / PVC; 2 x 0.5 mm²

Connection



BK =

Core colors :
black